

# SSH-XL



SnapStak® Plus Adjustable Hanger for 36mm to 51mm Cable - No Grommets Required. For patents, see [www.cs-pat.com](http://www.cs-pat.com).

## Product Classification

<b>Brand</b>	SnapStak® Plus
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Compatible Diameter, maximum</b>	51.000 mm   2.008 in
<b>Compatible Diameter, minimum</b>	36.000 mm   1.417 in
<b>Height</b>	88.00 mm   3.46 in
<b>Length</b>	99.00 mm   3.90 in
<b>Width</b>	41.00 mm   1.61 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Snap-in hanger
<b>Accessories</b>	Hangers
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Material Type</b>	Stainless steel
<b>Maximum Stack Height</b>	2
<b>Maximum Stack Height, Coaxial</b>	2
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada
<b>Package Quantity</b>	10
<b>Patent Number</b>	US 9,866,004

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	=1000 hours in salt spray chamber
<b>Flammability Test Method</b>	UL 2043
<b>Mounting</b>	3/4 in drilled cable ladder
<b>Vibration Survival</b>	=4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	304.8 mm   12.0 in
<b>Length</b>	254.0 mm   10.0 in
<b>Shipping Weight</b>	0.53 kg   1.17 lb
<b>Width</b>	15.0 cm   5.9 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power