



TTRC Copper Closure, unpressurized, gel sealed, 510 mm sheath opening, for up to 300 pair splices

- Watertight, toolless, torchless and re-usable closure for aerial applications
- Seals unpressurised inline splices in new construction and network maintenance applications up to 600 pairs
- Sealing on both the closure body and a multiple of cables is performed by compressing the gel material between two plastic flanges
- Gel compression is activated by a built-in tensing mechanism

Product Classification

| | |
|------------------------------|--------------------|
| Product Type | Gel sealed closure |
| Product Series | TTRC |
| Regional Availability | EMEA |

General Specifications

| | |
|--|----------------------------------|
| Application | For use with Polyethylene cables |
| Cable Capacity, maximum | 2 |
| Color | Black |
| Package, quantity | 1 |
| Packaging Type | Bag Carton |
| Single Cable Diameter, maximum | 26.00 mm 1.02 in |
| Single Cable Diameter, minimum | 10.00 mm 0.39 in |
| Splice Bundle Diameter, maximum | 126.00 mm 4.96 in |
| Splicing Capacity, maximum | 600 |

Dimensions

| | |
|-------------------------------|----------------------|
| Sheet Opening, nominal | 510.00 mm 20.08 in |
|-------------------------------|----------------------|

Mechanical Specifications

| | |
|---------------------------|------------|
| Cable Sealing Type | Gel filled |
| Closure Style | In-line |
| Mount Type | Strand |

Environmental Specifications

| | |
|----------------------------|--------|
| Environmental Space | Aerial |
|----------------------------|--------|

Regulatory Compliance/Certifications

| | |
|---------------|-----------------------|
| Agency | Classification |
|---------------|-----------------------|

RoHS 2011/65/EU

Compliant

