



Middle of Pole Pico Concealment Enclosure for low power remote micro radio heads

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

## Product Classification

**Product Type** Metro cell site enclosure

## Dimensions

**Depth** 304.8 mm | 12.0 in  
**Height** 1016.0 mm | 40.0 in  
**Weight (loaded)** 36.3 kg | 80.0 lb  
**Weight (unloaded)** 18.1 kg | 40.0 lb  
**Width** 401.3 mm | 15.8 in

## General Specifications

**Color** Light Grey (RAL 7035)  
**Color Notes** SSC-760236114xx1 - Light Grey | SSC-760236114xx2 - Green | SSC-760236114xx3 - Black | SSC-760236114xx4 - Brown  
**Color Options** Black | Brown (RAL 8014) | Green (RAL 6005)  
**Finish Aluminum** Chromate  
**Finish Concealment Covers** Powder coated  
**Material** Aluminum | Steel

## Electrical Specifications

**Power/Fiber Input** Trade size knockouts at rear side

## Antenna Specifications

**Antennas Included** None

## Radio Specifications

**Radio Compatibility, Ericsson** (1) 4415/4426 Radio & (1) 2203/2205/2208 | (6) 2203/2205/2208 radios  
**Radio Compatibility, Nokia** (1) Airscale Dual Band 160W + (1) AirScale micro radio | (1) DC Rectifier (Nokia FPAE OR Delta 1kw or 1.8kW) | SSC-760236114N2x | SSC-760236114N3x | Up to (4) AirScale micro radios

# SSC-760236114 | Pico Radio Enclosure

---

**Radios Included**                      None

## Mechanical Specifications

**Mounting Options**                      Wood poles | Tapered poles | Non-tapered poles

## Environmental Specifications

**Cooling**                                      Passive Cooling

**Thermal Compliance**                      GR-487

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

