

MC-FM4-24-278



4-sector Monopole 24" Stand-off Mount kit, 10 in to 30 in OD, includes (4) 2-7/8" OD x 96" pipe

Product Classification

Product Type Stand-off mount

General Specifications

Mounting Monopole, 254–762 mm (10–30 in) OD

Pipe, quantity 4

Sectors, quantity 4

Dimensions

Height 2,438.4 mm | 96 in

Face Width 0 m | 0 ft

Pipe Length 2,438.4 mm | 96 in

Mounting Diameter, maximum 762 mm | 30 in

Mounting Diameter, minimum 254 mm | 10 in

Pipe Outer Diameter 73.025 mm | 2.875 in

Stand-off Distance 609.6 mm | 24 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Pipe mounts | Plain end pipes (4) | Ring mount | Stand-off arms

Packaging quantity 1

Weight, net 260.453 kg | 574.2 lb