

760259115 | PPL-1U-ANG-FX



Propel 1RU fixed tray angled fiber panel, accepts Propel ULL components, providing up to 72 duplex LC ports, 72 MPO ports or 144 SN ports (288f). For use with 8 fiber, 12 fiber or 24 fiber components

- Components can be installed and removed from front or rear of panel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Brand	Propel
Product Series	PPL

General Specifications

Color	Gray
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed
Total Ports, quantity	0

Dimensions

Height	44 mm 1.732 in
Width	483 mm 19.016 in
Depth	236 mm 9.291 in

Material Specifications

Material Type	Aluminum Steel
----------------------	------------------

Environmental Specifications

Safety Standard	c-UL-us
------------------------	---------

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

