


FJ-12S5-UFAN



.HELIAX® Discrete, outdoor rated, single mode fiber cable assembly, End 1: Uniboot LC. End 2: HMFOC (Plug). At End 1, pre-install weatherproof shroud (EAS shroud) which can provide IP65 rating for spare branch protection.

HELIAX® Discrete, outdoor rated, single mode fiber cable assembly, End 1: Uniboot LC. End 2: HMFOC (Plug). At End 1, pre-install weatherproof shroud (EAS shroud) which can provide IP65 rating for spare branch protection. End 1 will connect to Radio and End 2 will connect to Middle trunk HMFOC (Jack)-HMFOC (Jack).

Page 1 of 2

Main cable length: 0.5m; Branch cable length: 1.5m, total cable assembly length 2m

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	FJ
Ordering Note	ANDREW® non-standard product

General Specifications


Construction Type	Direct fiber tail
Interface, Connector A	LC
Interface Body Style, connector A	Straight
Interface, Connector B	HMFOC
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	12

Dimensions

Breakout Length, connector A	99.822 mm 3.93 in
Cable Assembly Length	3.048 m 10 ft
Diameter Over Jacket	5.4 mm 0.213 in

Ordering Tree

FJ-12S5-UFAN



Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, loaded 108 mm | 4.252 in

Minimum Bend Radius, unloaded 54 mm | 2.126 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.3 dB

Return Loss, minimum, connector A 60 dB

FJ-12S5-UFAN

Return Loss, minimum, connector B 50 dB

Environmental Specifications

Installation temperature -30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Environmental Space Indoor/Outdoor

Jacket UV Resistance UV stabilized

Packaging and Weights

Cable weight 29 kg/km | 19.487 lb/kft

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)