



REGAL RLS 1.2 GHz RF splitter, 3 unbalanced outputs, AC power# passing, with surge protection

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

- Support DOCSIS® 3.1 expanded bandwidth up to 1218 MHz
- Maintain existing Regal installed base with compatible faceplate upgrades
- Easily configured to enable or block AC power as needed in the network
- Faceplate only options for cost-effective upgrades to existing Regal deployments
- Support aerial or pedestal installation with flexible design
- Protect valuable network equipment investment with heavy surge suppression options available

## Product Classification

|                       |   |
|-----------------------|---|
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| Product Type          | Splitter  |
| Product Series        | REGAL   |
| Government Funding    | Build America Buy America (BABA) compliant*                         |

## General Specifications

|                           |   |
|---------------------------|---|
| Location of Manufacturing | Waived per BABA waiver for BEAD Program |
|---------------------------|---|

## Dimensions

|        |                    |
|--------|--------------------|
| Height | 116.84 mm   4.6 in |
| Depth  | 76.2 mm   3 in     |
| Length | 139.7 mm   5.5 in  |

## Electrical Specifications

|                            |              |
|----------------------------|--------------|
| Current Handling, ac ports | 20 A         |
| Current Handling, RF ports | 15 A         |
| Operating Frequency Band   | 5 – 1218 MHz |
| Surge Protection           | Yes          |

Environmental Specifications

**Operating Temperature** -40 °C to +60 °C (-40 °F to +140 °F)

Packaging and Weights

**Weight** 0.68 kg | 1.5 lb

Regulatory Compliance/Certifications

| Agency     | Classification                    |
|------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS       | Compliant/Exempted                |
| UK-ROHS    | Compliant/Exempted                |

