



Indoor/Outdoor Fiber Optic Drop cable, 1 Fiber G657.B3 0.9mm tight buffer. Breaking load Max 2000N. Suitable for installation under overhead power lines  $\leq 11\text{kV}$ , vertical clearance  $\geq 1.8\text{m}$ .

Fire retardant Outside plant LSZH jacket grade, suitable for drop / aerial installations of up to 68 m. Can be routed indoor.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable


## General Specifications

<b>Cable Type</b>	Drop   Tight buffer
<b>Construction Type</b>	All Dielectric   Non-armored
<b>Subunit Type</b>	Gel-free
<b>Jacket Color</b>	White
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE 810010113/DB 1x G657A2 SM LSZH [DOM] [SERIAL NUMBER] [METER MARK]
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	1
<b>Total Fiber Count</b>	1

## Dimensions

<b>Cable Length</b>	1000 m   3,280.84 ft
<b>Buffer Tube/Subunit Diameter</b>	0.9 mm   0.035 in
<b>Diameter Over Jacket</b>	3 mm   0.118 in

## Representative Image



## Material Specifications

**Jacket Material** Low Smoke Zero Halogen (LSZH)

## Mechanical Specifications

**Minimum Bend Radius, loaded** 30 mm | 1.181 in

**Tensile Load, long term, maximum** 300 N | 67.443 lbf

**Tensile Load, short term, maximum** 620 N | 139.382 lbf

**Compression** 20 N/mm | 114.203 lb/in

**Compression Test Method** IEC 60794-1 E3

**Impact** 2 N-m | 17.701 in lb

**Impact Test Method** IEC 60794-1 E4

**Strain** See long and short term tensile loads

**Strain Test Method** IEC 60794-1 E1

**Twist** 10 cycles

**Twist Test Method** IEC 60794-1 E7

## Optical Specifications

**Fiber Type** G.657.B3

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +40 °C (+32 °F to +104 °F)
<b>Operating Temperature</b>	0 °C to +70 °C (+32 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Cable Qualification Standards</b>	IEC 60794-1-2
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Cca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1a
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d0
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a2
<b>Environmental Space</b>	Aerial   Drop   Ducted   Indoor/Outdoor
<b>Flame Test Listing</b>	EN 50399
<b>Flame Test Method</b>	IEC 60332-1-2   IEC 60754-2   IEC 61034-2
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5

## Environmental Test Specifications

<b>Temperature Cycle</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-22 F1

## Packaging and Weights

<b>Cable weight</b>	8.7 kg/km   5.846 lb/kft
<b>Packaging Type</b>	CablePak®   Reel in box

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

CS-8V2-MP	–	Enhanced Low Macrobending, Low Water Peak, Dispersion-Unshifted Single-mode Fiber
-----------	---	---

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable