

F075KLS3



FlexTwist® Flexible Twist for WR75, 10.0–15.0 GHz, with interface types PBR120 and UDR120, 900 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	PBR120
Interface 2	UDR120

Dimensions

Length	900 mm 35.433 in
Waveguide Size	WR75 WG17 R120

Electrical Specifications

Attenuation	0.59 dB/m 0.18 dB/ft
Average Power	750 W
Operating Frequency Band	10.0 – 15.0 GHz
Peak Power	140 kW
VSWR	1.1

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	64 mm 2.52 in
Minimum Bend Radius, Multiple Bends (H Plane)	115 mm 4.528 in
Maximum Twist	360 °/m 109.728 °/ft
Pressurization, maximum	0.31 N/mm ² 45 psi

F075KLS3

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

