

CNT-300A



CNT-300, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket

Product Classification

Product Type	Braided coaxial cable
Product Brand	CNT®
Product Series	CNT-300

General Specifications

Braid Coverage	87 %
Cable Type	CNT-300
Jacket Color	Black

Dimensions

Diameter Over Dielectric	4.83 mm 0.19 in
Diameter Over Jacket	7.62 mm 0.3 in
Diameter Over Tape	5.003 mm 0.197 in
Inner Conductor OD	1.78 mm 0.07 in
Outer Conductor OD	5.66 mm 0.223 in
Nominal Size	0.300 in

Electrical Specifications

Cable Impedance	50 ohm
Capacitance	80.4 pF/m 24.506 pF/ft
dc Resistance, Inner Conductor	11.05 ohms/km 3.368 ohms/kft
dc Resistance, Outer Conductor	8.5 ohms/km 2.591 ohms/kft
dc Test Voltage	2500 V
Jacket Spark Test Voltage (rms)	3500 V
Maximum Frequency	24.5 GHz
Operating Frequency Band	30 – 6000 MHz
Peak Power	10 kW

CNT-300A

Shielding Effectiveness	90 dB
Velocity	83 %

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
30.0	3.8	1.16
50.0	4.9	1.5
220.0	9.5	2.9
450.0	13.1	4
900.0	19.4	5.9
1500.0	25.3	7.7
1800.0	28.2	8.6
2000.0	29.8	9.1
2500.0	33.8	10.3
3000.0	37.4	11.4
4000.0	44.61	13.6
4500.0	47.75	14.55
5000.0	50.52	15.4
5200.0	51.83	15.8
5500.0	53.14	16.2
5800.0	54.78	16.7
6000.0	55.8	17

Material Specifications

Braid Material	Tinned copper
Dielectric Material	Foam PE
Jacket Material	PE
Inner Conductor Material	Copper-clad aluminum wire
Shield Tape Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, single Bend	22.352 mm 0.88 in
Tensile Strength	23 kg 50.706 lb
Bending Moment	0.5 N-m 4.425 in lb
Flat Plate Crush Strength	0.5 kg/mm 27.999 lb/in

CNT-300A

Environmental Specifications

Installation temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)

Packaging and Weights

Cable weight	0.06 kg/m 0.04 lb/ft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

