EWP52S



EWP52, HELIAX® Super Premium Elliptical Waveguide, 5.925–6.425 GHz, black PE jacket

OBSOLETE

Product Classification

Product Type Super premium elliptical waveguide

Product Brand HELIAX®

Product Series Super Premium

General Specifications

Jacket Color Black

Performance Note Values typical, unless otherwise stated

Dimensions

Diameter Over Jacket (E Plane)57.2 mm | 2.252 inDiameter Over Jacket (H Plane)33.3 mm | 1.311 in

Cable Volume 1045 L/km | 11.248 ft³/kft

Electrical Specifications

eTE11 Mode Cutoff 3.65 GHz

Operating Frequency Band 5.925 – 6.425 GHz

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

5.925–6.425 GHz 1.05 32.3

Attenuation

Frequency (GHz) Attenuation (dB/100 m) Attenuation (dB/100 ft) Average Power (kW) Group Velocity %

5.925 3.965 1.209 5.917 78.8

ANDREW®

EWP52S

6.13	3.887	1.185	6.037	80.3
6.33	3.822	1.165	6.138	81.7

Material Specifications

Conductor Material Corrugated copper

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	305 mm 12.008 in
Minimum Bend Radius, Multiple Bends (H Plane)	810 mm 31.89 in
Minimum Bend Radius, Single Bend (E Plane)	200 mm 7.874 in
Minimum Bend Radius, Single Bend (H Plane)	560 mm 22.047 in
Maximum Twist	3.281 °/m 1 °/ft

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)

Attenuation, Ambient Temperature $75 \,^{\circ}\text{F}$ | $23.889 \,^{\circ}\text{C}$ Average Power, Ambient Temperature $104 \,^{\circ}\text{F}$ | $40 \,^{\circ}\text{C}$ Average Power, Temperature Rise $42 \,^{\circ}\text{C}$ | $107.6 \,^{\circ}\text{F}$

Packaging and Weights

Cable weight 0.88 kg/m | 0.591 lb/ft

Regulatory Compliance/Certifications

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

