## 5248003 | POWER FEEDER® 625 JCASST 3R



23 Ohm Power Feeder® Trunk and Distribution Cable, black PE jacket with three co-extruded red stripes, flooded for underground

\*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## **Product Classification**

Regional Availability North America

Product Type Coaxial hardline cable

Product Brand Power Feeder®

**Government Requirements**Build America Buy America (BABA) compliant\*

**Warranty** One year

General Specifications

Cable Type625 SeriesConstruction TypeSwaged

**Jacket Color**Black with three co-extruded red stripes

**Location of Manufacturing**Catawba, North Carolina

**Short Description** PF 625 JCASST 3R SM PR1921

Dimensions

Cable Length731.52 m | 2400 ftDiameter Over Center Conductor, nominal8.255 mm | 0.325 inDiameter Over Dielectric, nominal13.081 mm | 0.515 inDiameter Over Jacket, nominal17.653 mm | 0.695 inDiameter Over Outer Conductor, nominal15.875 mm | 0.625 inJacket Thickness, nominal0.762 mm | 0.03 inOuter Conductor Thickness, nominal1.397 mm | 0.055 in

**Electrical Specifications** 

**Characteristic Impedance** 23 ohm



## 5248003 | POWER FEEDER® 625 JCASST 3R

dc Resistance Note Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal0.525 ohms/km | 0.16 ohms/kftdc Resistance, Loop, nominal0.984 ohms/km | 0.3 ohms/kft

dc Resistance, Outer Conductor, nominal 0.459 ohms/km | 0.14 ohms/kft

Jacket Spark Test Voltage 5000 Vac

Material Specifications

Center Conductor Material Copper-clad aluminum

**Dielectric Material** Foam PE

Jacket Material PE

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, standard 228.6 mm | 9 in

**Pulling Tension, maximum** 362.874 kg | 800 lb

**Environmental Specifications** 

Corrosion Protection Migraheal®

Environmental Space Buried

Packaging and Weights

Packaging Type Reel

**Weight, gross** 547.644 kg/km | 368 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



