

HELIAX® Hybrid Cable, UL Type TC-OF-ER

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

Hybrid cable, copper and fiber

Product Brand

HELIAX®

General Specifications

Application

Remote radio head

Cable Type

Wireless feeder

Conductors, quantity

6

Construction Type

Shielded

Fiber Short Description

RFF – 12AWG

Fiber Type, quantity

24

Fibers per Subunit, quantity

12

Inner Shield (Tape) Material

Corrugated aluminum

Jacket Color

Black

Outer Shield (Tape) Material

PVC

Strength Members

Glass reinforced plastic rod

Subunit, quantity

2

Total Fiber Count

24

Water Blocking Method

Water blocking tape(s) | Water blocking threads

Dimensions

Buffer Tube/Subunit Diameter

3.048 mm | 0.12 in

760235001 | HTC-24SM-1212-APVA

Diameter Over Jacket 23.876 mm | 0.94 in


Conductor Gauge 12 AWG

Electrical Specifications

dc Resistance Note Maximum value based on a standard condition of 20 °C (68 °F)

dc Resistance, maximum 5.413 ohms/km | 1.65 ohms/kft

Representative Image



Material Specifications

Ripcord Material Para-aramid synthetic fiber

Mechanical Specifications

Minimum Bend Radius, multiple bends, loaded 474.98 mm | 18.7 in

Minimum Bend Radius, multiple bends, unloaded 284.48 mm | 11.2 in

Minimum Bend Radius, single bend, unloaded 167.64 mm | 6.6 in

Tensile Load, long term, maximum 2,668.932 N | 600 lbf

Tensile Load, short term, maximum 800.68 N | 180 lbf

Compression 2.25 kg/mm | 126 lb/in

Compression Test Method FOTP-41

Flex 25 cycles

Flex Test Method FOTP-104

Impact 2.17 ft lb | 2.942 N-m

Impact Test Method FOTP-25

Twist 10 cycles

Twist Test Method FOTP-85

760235001 | HTC-24SM-1212-APVA

Optical Specifications

Fiber Type G.657.A2/B2 | OM2+, LazrSPEED® 150

Environmental Specifications

Installation temperature -30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20 | Telcordia GR-409

Environmental Space Wireless installation

Packaging and Weights

Cable weight 806.138 kg/km | 541.7 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

CS-5M-MP – LazrSPEED® 150 OM2+ Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable