
# 760067264 | P-002-ZC-8W-F16YL



Fiber indoor cable, TeraSPEED® 1.6 mm Plenum Zipcord, Singlemode G. 652.D and G.657.A1, Feet jacket marking, Yellow jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

**Product Type** Fiber indoor cable

Product Series P-ZC

### General Specifications

Cable TypeCordage

Construction Type Non-armored

**Subunit Type** Gel-free

**Jacket Color** Yellow

Jacket Marking Feet

**Total Fiber Count** 2


#### Dimensions

Height Over Jacket1.7 mm | 0.067 inWidth Over Jacket3.5 mm | 0.138 in

## Representative Image



# 760067264 | P-002-ZC-8W-F16YL



#### Mechanical Specifications

Minimum Bend Radius, loaded38 mm | 1.496 inMinimum Bend Radius, unloaded15 mm | 0.591 inTensile Load, long term, maximum53 N | 11.915 lbfTensile Load, short term, maximum178 N | 40.016 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 500 m | 1,640.42 ft

Optical Specifications

**Fiber Type** G.652.D and G.657.A1, TeraSPEED®

### **Environmental Specifications**

**Installation temperature** 0 °C to +70 °C (+32 °F to +158 °F)

**COMMSCOPE®** 

# 760067264 | P-002-ZC-8W-F16YL

**Operating Temperature**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$ 

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

**Environmental Space** Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

## **Environmental Test Specifications**

**Heat Age**  $-20 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-20 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 6 kg/km | 4.032 lb/kft

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-8W-TB - TeraSPEED® Singlemode Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

