

# A-100197

---

## Base Product



## Combiner/ Mast head amplifier enclosure for micro cell sites

- Sealed to outside environment
- Double wall construction

## Product Classification

<b>Product Type</b>	Micro cell site enclosure
<b>Ordering Note</b>	For UK region only

## General Specifications

<b>Access</b>	Front door
<b>Batteries Supported</b>	0
<b>Cabinet Type</b>	Combiner cabinet
<b>Color</b>	Green (RAL 6009)   Light Gray (RAL 7035)   Others available at additional cost
<b>Door Security</b>	Swing handle with 22mm profile cylinder
<b>Doors, quantity</b>	1
<b>Mounting</b>	Plinth   Root

## Dimensions

<b>Height</b>	1143 mm   45 in
<b>Width</b>	762 mm   30 in
<b>Depth</b>	355.6 mm   14 in

## Electrical Specifications

<b>Generator Connection</b>	No connection
<b>Rectifiers, quantity</b>	0

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## Environmental Specifications

# A-100197

---

**Qualification Standards** IEC 60529: 2001 | IEE Wiring Regulations BS 7671 | IP45

## Packaging and Weights

**Included** Brackets | Installation Kit

**Weight, net** 49.895 kg | 110 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system