


FDT-GJ212NXB0000



OFDT Outdoor Fiber Distribution Terminal, 24-fiber, SC/APC, 12 ports loaded, 2 splice trays, with pigtails

- OFDT is a compact and secure family of enclosures by connecting fiber cables at MDUs
- Features a unique “swing frame” type design that separates the splicing in the rear from the patch access in the front
- Accommodates a variety of OSP cable types via sealed grommet entry with standard grip clamps
- Robust steel construction protects fibers against damage and ensures network reliability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	OFDT

General Specifications

Functionality	Patching Splicing
Access	Front
Cable Type	Pigtails - Stranded
Enclosure Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Partially loaded
Interface	SC/APC
Lock Type	Padlock ready
Mounting	Wall
Port Capacity, maximum	24
Port, quantity	12

Dimensions

Height	342.9 mm 13.5 in
Width	482.6 mm 19 in
Depth	203.2 mm 8 in

Material Specifications

Enclosure Material Type	Steel
--------------------------------	-------

FDT-GJ212NXB0000

Finish Powder coated

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Outdoor

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant

