

PRO PATCH® Integrated Standard Size Video Panel, 2 RU, 3 x 26

OBSOLETE

This product was discontinued on: December 31, 2018

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Video patch panel
Product Brand	PRO PATCH®
Product Series	ProPatch

General Specifications

Application	For use with WECO HD standard size video patch cords
Color	Black
Growth Configuration	Fully loaded
Interface, front	SVJ-2 jack
Interface, rear	BNC female adapter
Mounting	Rack, horizontally oriented
Rack Type	EIA 19 in
Rack Units	2
Total Ports, quantity	78

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Electrical Specifications

Characteristic Impedance	75 ohm
---------------------------------	--------

Material Specifications

Finish	Powder coated
Material Type	Steel

Mechanical Specifications

Plug Insertion Force, maximum	12 N 2.698 lbf
Plug Insertion Life, minimum	20000 times
Plug Retention Force, minimum	3 N 0.674 lbf

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Relative Humidity	Up to 95%, non-condensing
Environmental Standard	MIL-STD-202
Flammability Rating	UL 94 V-0

Packaging and Weights

Included	Designation strips
-----------------	--------------------

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance