

760093393 | 360-iP-HD-MOD-LC-OS-3



SYSTIMAX 360™ iPatch® G2 Multimode OM1 High Density Module, 3 pack

OBSOLETE

This product was discontinued on: March 1, 2018

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	OptiSPEED® SYSTIMAX 360™ iPatch®

General Specifications

Functionality	Breakout
Adapters, quantity, rear	12
Color, front	Beige
Color, housing	Black
Color, rear	Black
Intelligence Type	iPatch® enabled
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Reduced footprint
Total Ports, quantity, front	144

Dimensions

Height	82.55 mm 3.25 in
Width	152.4 mm 6 in
Depth	215.9 mm 8.5 in

Material Specifications

760093393 | 360-iP-HD-MOD-LC-OS-3

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

Optical Specifications

Fiber Type OM1
Insertion Loss Change, mating 0.3 dB
Insertion Loss Change, temperature 0.3 dB
Insertion Loss, maximum 0.85 dB

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity Up to 95%, non-condensing
Flammability Rating UL 94 V-0
Safety Standard ACMA | CE | CSA | UL

Packaging and Weights

Packaging quantity 3
Weight, net 1.13 kg | 2.491 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss Change, mating Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)