# NGF-VSPM-7000R



Next Generation Frame (NGF) Fiber MicroVAM Block, unloaded, putty white, right orented

#### **Product Classification**

Regional Availability EMEA | Latin America | North America

**Product Type** Fiber VAM block

**Product Series** NGF

General Specifications

Functionality Multiplexing | Splitting

**Application** Used in NGF-style frames only

**Body Style** Right orientation

ColorPutty whiteColor, frontPutty white

Door Type, front Compression latch | Hinged

Growth Configuration Unloaded

Module/Adapter Pack Slots, quantity12Rack TypeNGFShelf MovementFixed

**Dimensions** 

 Height
 299.72 mm | 11.8 in

 Width
 454.914 mm | 17.91 in

 Depth
 132.08 mm | 5.2 in

Material Specifications

**Finish** Powder coated

Material Type Steel

COMMSCOPE®

## NGF-VSPM-7000R

### **Environmental Specifications**

**Operating Temperature**  $-5 \,^{\circ}\text{C}$  to  $+50 \,^{\circ}\text{C}$  ( $+23 \,^{\circ}\text{F}$  to  $+122 \,^{\circ}\text{F}$ )

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 80%, non-condensing

**Qualification Standards** Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

