

GigaSPEED X10D® 1100GS5 Category 6A U/UTP 2U Panel Kit

OBSOLETE

Replaced By:

760105312
1100-GS6-2U

GigaSPEED X10D® 1100GS6 Category 6A U/UTP 2U Panel Kit

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

Product Brand

GigaSPEED X10D®

General Specifications

Cable Type

Unshielded

Color

Black

Conductor Type

Solid | Stranded

Intelligence Type

Passive

Panel Style

Straight

Rack Type

EIA 19 in

Rack Units

2

Dimensions

Height

88.9 mm | 3.5 in

Width

482.6 mm | 19 in

Depth

40.64 mm | 1.6 in

Compatible Conductor Gauge, solid

22 AWG | 24 AWG

Compatible Conductor Gauge, stranded

22 AWG | 24 AWG

Electrical Specifications

Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

Dielectric Withstand Voltage, RMS, contact-to-contact 1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Material Specifications

Material Type Powder-coated steel

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

