

TTRC Copper Closure, unpressurized, gel sealed, 510 mm sheath opening, for up to 300 pair splices



- Watertight, toolless, torchless and re-usable closure for aerial applications
- Seals unpressurised inline splices in new construction and network maintenance applications up to 600 pairs
- Sealing on both the closure body and a multiple of cables is performed by compressing the gel material between two plastic flanges
- Gel compression is activated by a built-in tensioning mechanism

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Gel sealed closure
<b>Product Series</b>	TTRC

## General Specifications

<b>Application</b>	For use with Polyethylene cables
<b>Cable Capacity, maximum</b>	2
<b>Cable Sealing Type</b>	Gel filled
<b>Closure Style</b>	In-line
<b>Color</b>	Black
<b>Mounting</b>	Strand
<b>Splicing Capacity, maximum</b>	300

## Dimensions

<b>Single Cable Diameter, maximum</b>	21 mm   0.827 in
<b>Single Cable Diameter, minimum</b>	10 mm   0.394 in
<b>Splice Bundle Diameter, maximum</b>	92 mm   3.622 in
<b>Sheath Opening, nominal</b>	510 mm   20.079 in

## Environmental Specifications

**Environmental Space** Aerial

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

