

# BM4894-000 | FOSC-400-B4-A-BJL-4-L-48F



## FOSC® 400 B4 Fiber Optic Splice Closure, Heat Shrink Cable sealing,

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

## Product Classification

<b>Regional Availability</b>	Asia   EMEA
<b>Product Type</b>	Single-ended, round fiber closure
<b>Product Brand</b>	FOSC®
<b>Product Series</b>	FOSC 400

## General Specifications

<b>Cable Entry Drop Port Style</b>	Round
<b>Cable Entry Main Port Style</b>	Oval
<b>Cable Ports Quantity, total</b>	1 oval port (2 cables) + 4 round ports
<b>Cable Sealing Type</b>	Heat shrink
<b>Closure Sealing Type</b>	Dome-to-base clamp with O-ring
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Pole   Strand   Wall
<b>Network Area Type</b>	Feeder
<b>Splicing Capacity, Mass Fusion, maximum</b>	144
<b>Splicing Capacity, Single Fusion, maximum</b>	96
<b>Splicing Capacity, Single Splice, 12 fibers, maximum</b>	96
<b>Splicing Capacity, Single Splice, 6 fibers, maximum</b>	48
<b>Splicing Type, Supported</b>	Single fusion

## Dimensions

<b>Length</b>	540 mm   21.26 in
<b>Diameter</b>	150 mm   5.906 in

# BM4894-000 | FOSC-400-B4-A-BJL-4-L-48F


**Diameter, with clamp**

180 mm | 7.087 in

**Main Cable Diameter, maximum**

25 mm | 0.984 in

## Dimension Drawing



## Ordering Tree

# BM4894-000 | FOSC-400-B4-A-BJL-4-L-48F

FOSC - 400 X - X - X - X X X

## Closure size

A4	420mm - 4 round ports
B4	540mm - 4 round ports
D5	710mm - 5 round ports
A8	410mm - 8 round ports <sup>14</sup>
A5	420mm - 4 round ports
B2	540mm - 2 round ports
D5/B	505mm - 5 round ports

## Tray type

NT		Splices in splice protectors at tray exterior			
		A4	A8	B2, B4, D5/B	D5
S12	12 SMOUV splice protectors (4.5mm)			X	
S24	24 SMOUV splice protectors (4.5mm)	X	X	X	
A24	24 ANT splice protectors	X	X	X	
4R4	4 splice protectors for ribbon cable with 4 fibers	X	X		
6R4	6 splice protectors for ribbon cable with 4 fibers			X	
		Splices stored in modules at tray interior			
		A4	A8	B2, B4, D5/B	D5
12	12 splice protectors (2 modules, 6 splices/module)	X	X	X	
24	24 splice protectors (2 modules, 12 splices/module)	X	X	X	
36	36 splice protectors (6 modules, 6 splices/module)				X
S96	96 SMOUV splice protectors (4.5mm)				X
I96	96 SMOUV splice protectors (60 mm)				X
A96	96 ANT splice protectors				X
RT24	24 splices for ribbon cable with 12 fibers (4 modules, 6 splices/module)				X

## Flash test valve

V	Pre-installed flash test valve
N	No flash test valve

## Ground feedthrough

G	Pre-installed ground feedthrough
N	No ground feedthrough

## Moisture cable blocking

N	No blocking
B	Blocking

## Number of splice trays

0	No trays
Closure size	
1...3	A4
1...4/8	A8 <sup>14</sup>
1...6	B <sup>14</sup>
1...12	D5/B <sup>14</sup>
1...8	D5 <sup>14</sup>

<sup>14</sup> A8 closure can accept a mix of standard and slim trays; please contact your local sales representative.

<sup>15</sup> Maximum 8 trays in case of S6 or A6 tray type

<sup>16</sup> B closure can initially be fitted with trays; however, retrofitting a standard "B" closure (delivered with 4 trays or fewer) with a 5th and 6th tray is not possible. The B closure can be ordered with up to 5 trays pre-installed and capacity for later addition of a 6th tray (FOSC-400B4XXX/6...).

If 5 or 6 trays are required, a storage basket cannot be used.

<sup>17</sup> If 7 or 8 trays are required, a storage basket cannot be used.

## Material Specifications

### Material Type

Impact-resistant polymer

## Environmental Specifications

### Environmental Space

Below ground | Buried

### Qualification Standards

IEC 61300, 6 m waterhead

## Packaging and Weights

### Packaging quantity

1

### Packaging Type

Box | Carton

### Weight, net

2.5 kg | 5.512 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

REACH-SVHC

**Classification**

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)