

# FL2-S2702A150-AU00

---



FL2000 Fiber Termination Panel, 24 SC/UPC, singlemode, 2RU, 19 in, putty white, pre-terminated with IFC cable, 150 meters, Stub tail at far end

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel, with IFC cable
<b>Product Series</b>	FL2000

## General Specifications


<b>Functionality</b>	Patching
<b>Adapter Packs Included, quantity</b>	4
<b>Cable Exit Location</b>	Upward
<b>Cable Stub Type</b>	IFC
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	SC/UPC
<b>Interface, rear</b>	Stub tail
<b>Patching Capacity, maximum</b>	24
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Hinged
<b>Splicing Capacity, maximum</b>	0
<b>Total Ports, quantity</b>	24

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	256.54 mm   10.1 in
<b>Cable Length</b>	150 m   492.126 ft

# FL2-S2702A150-AU00

## Ordering Tree



## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

# FL2-S2702A150-AU00

---

**Packaging quantity**

1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

