

NGF-CB2CR221082



Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 96 FC/UPC, singlemode, right oriented, putty white

OBSOLETE

This product was discontinued on: **March 1, 2018**

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber patch/splice block
Product Series	NGF

General Specifications

Functionality	Patching Splicing
Application	Used in NGF-style frames only
Body Style	Right orientation
Cable Exit Location	Rear, bottom side
Color	Putty white
Color, front	Putty white
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	FC/UPC
Rack Type	NGF
Shelf Movement	Fixed
Total Ports, quantity	96

Dimensions

Height	558.8 mm 22 in
---------------	------------------

NGF-CB2CR221082

Width 166.878 mm | 6.57 in

Depth 495.3 mm | 19.5 in

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

