196948-000 | FOMS-FPS-0-SIS1-12

FOMS-FPS Fiber Termination/Splice Panel, 12 SC/UPC, singlemode, 1RU, 19 in, gray

Product Classification

| Regional Availability | EMEA | | | |
|-----------------------|--------------------------|--|--|--|
| Portfolio | CommScope® | | | |
| Product Type | Fiber patch/splice panel | | | |
| Product Series | FOMS-FPS | | | |

General Specifications

| Functionality | Patching Splicing |
|-----------------------|-------------------------------------|
| Color | Gray |
| Color, front | Gray |
| Interface, front | SC/UPC |
| Rack Type | EIA 19 in EIA 23 in ETSI 600 mm |
| Rack Units | 1 |
| Shelf Movement | Hinged |
| Total Ports, quantity | 12 |
| Dimensions | |
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |

Ordering Tree

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2023



196948-000 | FOMS-FPS-0-SIS1-12

FOMS-FPS - X - X X XX - XX

| Chase | | | | | | | Numbe | er of pigtail | | | | |
|---|------------------------------|---------------------|----------------|---------------------------------|----------------------|-------------|-------|---------------|-------|-------|----|----|
| | 0 19" - 44 mm high | | | | | | 48 | (for LC an | d MU | only) | | |
| Shelf | type | | | | | | 24 | | | | | |
| P Patching only (jumpers, break-out cable) | | | | | | | 16 | (not for LC | and M | AU) | | |
| S Splicing and patching (loose tube cable, ribbon, IFC) | | | | | 12 | (not for LC | and M | AU) | | | | |
| _ | | | | | | | 0 | | | | | |
| | ype/pigtails | | | 1.10 | Connector adaptor | unith rot | ainer | | | | | |
| Secondary coated pigtails | | Splice protector | | connector adapter with retainer | | | | | | | | |
| 0185582 | included | protector | Right front | Left front | NN No connector | | | | | | | |
| Not a | applicable (patching only) | | N | M | Min.return loss | SC | FC | E2000 | LC | DIN | ST | M |
| | No | SMOUV* | E | G | Single Mode Standard | | | | | | | |
| | No | ANT* | F | н | 45 dB (PC) | | | | | DO | TO | |
| Yes | | SMOUV* | 1 | K | 50 dB (UPC) | S1 | F1 | | L1 | | | UI |
| | Yes | ANT* | J | L | 60 dB (APC 8°) | S2 | F2 | E9 | L2 | | | |
| | | | | | 60 dB (APC 9°) | \$3 | | | | | | |
| Solic | e protectors not included ir | a tha kit | | | Single Mode Low I | .oss | | | | | | |
| * In case of adapters only (no pigtails included) use S5D, 5D, E5D, L5D and T5D. | | | 50 dB (UPC) | S6 | | | | | | T | | |
| | | | 60 dB (APC 8°) | S7 | | E8 | | | | | | |
| | | | | | 60 dB (APC 9°) | S8 | | | | | | - |
| | | | | Single Mode Cons | umer Gr | ade | 1 | | | | -L | |
| | | | | | 50 dB (UPC) | SC | FC | | LC | | | Τ |
| | | | | | 60 dB (APC 8°) | SD | FD | | LD | | | - |
| | | | | | Multi Mode | | | 1 | | | | _ |

50/900 µ

Material Specifications

Material Type

Ethylene-propylene (EP) | Polyethylene terephthalate (PET)

62.5/900 µ** S5E F5E

S5D F5D

E5D L5D

ESE LSE

T5D

T5E

Optical Specifications

Fiber Mode

Singlemode

Packaging and Weights

- Included Mounting hardware
- Packaging quantity

1

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2023



196948-000 | FOMS-FPS-0-SIS1-12



Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2023

