

760038521 | iPatch-PTF-12-SC-TS



iPatch® TeraSPEED® Pre-Terminated Intelligent Fiber Panel, SC 12 port duplex

OBSOLETE

This product was discontinued on: December 31, 2012

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Brand	TeraSPEED® iPatch®

General Specifications

Color	Black
Intelligence Type	iPatch® enabled
Interface, front	SC/UPC
Rack Units	1
Shelf Movement	Sliding
Total Ports, quantity	12

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	323.85 mm 12.75 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
----------------------	--

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

760038521 | iP-PTF-12-SC-TS

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	ACMA CE CSA UL

Packaging and Weights

Included	Four #12-24 mounting screws Instruction sheet Shelf
Packaging quantity	1
Weight, net	3.175 kg 7 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

