

# 760188409 | 360G2-iP-2U-192F-LC-DM-OS-SD

SYSTIMAX 360™ iPatch® InstaPATCH 2U 192F-LC Distribution Module, OptiSPEED, Sliding Panel



**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber splice panel
<b>Product Brand</b>	SYSTIMAX 360™   iPatch®

## General Specifications

<b>Color</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, front</b>	LC
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	96

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	478.79 mm   18.85 in

## Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)
----------------------	--

## Optical Specifications

# 760188409 | 360G2-iP-2U-192F-LC-DM-OS-SD

---

**Fiber Mode** Multimode

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** Austel | CE | CSA | UL

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 5.897 kg | 13 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

