

RCPB-4TAPUT06125



RapidFiber® Termination Panel, 144-Position SC/UPC to MPO, 4RU, multimode (OM4), 61 m, black

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with rapid cable
Product Brand	RapidFiber®
Product Series	RCP

General Specifications

Functionality	Patching
Body Style	Symmetrical
Cable Exit Location	Rear, left side
Cable Stub Type	Indoor, microcable
Color	Black
Color, front	Black
Door Type, front	Hinged Slide latch Transparent
Growth Configuration	Fully loaded
Interface, front	SC
Interface Feature, front	Standard
Interface, rear	MPO
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	4
Shelf Movement	Sliding
Total Fibers, quantity	144


RCPB-4TAPUT06125

Total Ports, quantity 144
Transmission Standards IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

Dimensions

Height 177.8 mm | 7 in
Width 482.6 mm | 19 in
Depth 381 mm | 15 in
Cable Stub Length 61 m | 200.131 ft

Ordering Tree



ONLY FOR MULTIMODE VERSION.¹
 ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE²
 RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.³
 ONLY AVAILABLE IN LC288 4RU⁴

Material Specifications

Finish Powder coated

RCPB-4TAPUT06125

Material Type Steel

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, bend insensitive

Environmental Specifications

Operating Temperature -5 °C to +55 °C (+23 °F to +131 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

