

CBGGD | IP6A-12RUTP-PG1S-PG1S

Base Product



InstaPATCH® Cu GigaSPEED X10D® U/UTP Riser Preterminated Copper Cable, single row standard density RJ45 plug to single row standard density RJ45 plug, 12 links

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Copper trunk cable assembly |
| Product Brand | GigaSPEED X10D® InstaPATCH® Cu |

General Specifications

| | |
|---------------------------------------|-------------------------------|
| ANSI/TIA Category | 6A |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Solid |
| Interface, Connector A | RJ45 plug |
| Interface Feature, connector A | Single row Standard density |
| Interface, Connector B | RJ45 plug |
| Interface Feature, connector B | Single row Standard |
| Link Count | 12 |
| Wiring | T568B |

Dimensions

| | |
|---|---------|
| Cable Assembly Length Range (m) | 2 – 80 |
| Cable Assembly Length Range (ft) | 7 – 262 |

Electrical Specifications

| | |
|-------------------------------|---------|
| dc Resistance, maximum | 0.3 ohm |
| Safety Voltage Rating | 300 V |

Ordering Tree

CBGGD | IP6A-12RUTP-PG1S-PG1S

| | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|----|----|----|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | | | | |
| C | A | A | A | C | - | 1 | 1 | H | A | B | B | F | 0 | 5 | 0 |

| Cable Type | |
|------------|-------------------------------------|
| A | Cat 6A X10D – U/UTP (Plenum) |
| B | Cat 6A X10D – U/UTP (Riser) |
| C | Cat 6A X10D – U/UTP (LSZH) |
| D | Cat 6A X10D – F/UTP (Plenum) |
| E | Cat 6A X10D – F/UTP (Riser) |
| F | Cat 6A X10D – F/UTP (LSZH) |
| G | Cat 6 XL – U/UTP (Plenum) |
| H | Cat 6 XL – U/UTP (Riser) |
| J | Cat 6 XL – U/UTP (LSZH) |
| Q | Cat 6A X10D – S/FTP (LSZH) |
| R | Cat 6 – U/UTP Class B Rated (LSZH) |
| S | Cat 6A – U/UTP Class B Rated (LSZH) |
| Y | Cat 6A X10D SD – U/UTP (Riser) |

| Connector B | |
|-------------|--|
| A | Outlet* – Single Row Standard Density |
| B | Outlet* – Dual Row Standard Density |
| C | Outlet* – Dual Row High Density |
| G | RJ45 Plug* – Single Row Standard Density |
| H | RJ45 Plug* – Dual Row Standard Density |
| J | RJ45 Plug* – Dual Row High Density |
| N | 1100 Module |
| R | 360 1100 Evolve Module |
| S | OneLink 2x6 |
| T | OneLink 2x4 |

| Orientation A | |
|---------------|-----------------------|
| 1 | Trident Series Flat |
| 2 | Right Paired Flat |
| 3 | Right Series Flat |
| 4 | Left Paired Flat |
| 5 | Left Series Flat |
| 6 | Trident Paired Flat |
| A | Trident Series Angled |
| B | Right Paired Angled |
| C | Right Series Angled |
| D | Left Paired Angled |
| E | Left Series Angled |
| F | Trident Paired Angled |

| Orientation B | |
|---------------|-----------------------|
| 1 | Trident Series Flat |
| 2 | Right Paired Flat |
| 3 | Right Series Flat |
| 4 | Left Paired Flat |
| 5 | Left Series Flat |
| 6 | Trident Paired Flat |
| A | Trident Series Angled |
| B | Right Paired Angled |
| C | Right Series Angled |
| D | Left Paired Angled |
| E | Left Series Angled |
| F | Trident Paired Angled |
| X | Not Applicable |

| Link | |
|------|----|
| B | 6 |
| C | 8 |
| D | 12 |
| E | 16 |
| F | 18 |
| G | 24 |

| Outlet Color | |
|--------------|----------------|
| 0 | Not Applicable |
| 1 | Black (BK) |
| 2 | Blue (BL) |
| B | White (WH) |

| UOM | |
|-----|-------|
| F | Foot |
| M | Meter |

| Length | |
|--------|-----|
| 12 | XXX |

| Connector A | |
|-------------|--|
| A | Outlet* – Single Row Standard Density |
| B | Outlet* – Dual Row Standard Density |
| C | Outlet* – Dual Row High Density |
| H | RJ45 Plug* – Single Row Standard Density |
| G | RJ45 Plug* – Dual Row Standard Density |
| J | RJ45 Plug* – Dual Row High Density |
| N | 1100 Module |
| R | 360 1100 Evolve Module |
| S | OneLink 2x6 |
| T | OneLink 2x4 |
| X | Unterminated |

| Bundling | |
|----------|-------------|
| H | Hook-n-loop |
| S | Sleaving |

| Jacket Color | |
|--------------|------------|
| B | White (WH) |
| C | Slate (SL) |
| Z | Blue (BL) |

| Labeling | |
|----------|---------------|
| A | Generic Label |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Environmental Space | Riser |
| Flammability Rating | UL 94 V-0 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



Included Products

| | | |
|------------|---|---|
| 1095B-4/24 | – | GigaSPEED X10D® 1095B Category 6A U/UTP Cable, non-plenum, 4 pair count |
|------------|---|---|

1095B-4/24

GigaSPEED X10D® 1095B Category 6A U/UTP Cable, non-plenum, 4 pair count

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Twisted pair cable |
| Product Brand | GigaSPEED X10D® |


General Specifications

| | |
|--------------------------------|--------------------|
| Product Number | 1095B |
| ANSI/TIA Category | 6A |
| Cable Component Type | Cordage |
| Cable Type | U/UTP (unshielded) |
| Conductor Type, singles | Solid |
| Conductors, quantity | 8 |
| Pairs, quantity | 4 |
| Separator Type | Isolator |
| Transmission Standards | ANSI/TIA-568.2-D |

Dimensions

| | |
|--------------------------------------|---------------------|
| Diameter Over Jacket, nominal | 7.239 mm 0.285 in |
| Jacket Thickness | 1.524 mm 0.06 in |
| Conductor Gauge, singles | 24 AWG |

Cross Section Drawing



Electrical Specifications

| | |
|--|---|
| Characteristic Impedance | 100 ohm |
| Characteristic Impedance Tolerance | ±15 ohm |
| dc Resistance Unbalance, maximum | 4 % |
| dc Resistance, maximum | 9.38 ohms/100 m 2.859 ohms/100 ft |
| Dielectric Strength, minimum | 1500 Vac 2500 Vdc |
| Mutual Capacitance at Frequency | 6.0 nF/100 m @ 1 kHz |
| Nominal Velocity of Propagation (NVP) | 67 % |
| Operating Frequency, maximum | 550 MHz |
| Operating Voltage, maximum | 80 V |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |
| Safety Voltage Rating | 300 V |

Material Specifications

| | |
|----------------------------|-------------|
| Conductor Material | Bare copper |
| Insulation Material | Polyolefin |

1095B-4/24

| | |
|-----------------------------|------------|
| Jacket Material | PVC |
| Separator Material | Polyolefin |
| Separator 2 Material | Polyolefin |

Mechanical Specifications

| | |
|---------------------------------|------------------|
| Pulling Tension, maximum | 11.34 kg 25 lb |
|---------------------------------|------------------|

Environmental Specifications

| | |
|---------------------------------|-------------------------------------|
| Installation temperature | 0 °C to +60 °C (+32 °F to +140 °F) |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| Environmental Space | Non-plenum |
| Flame Test Method | CM |

Packaging and Weights

| | |
|---------------------|-----------------------------|
| Cable weight | 55.047 kg/km 36.99 lb/kft |
|---------------------|-----------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |