

# CBSXD | IP6A-12RUTP-1LK12-BLUNT

## Base Product



InstaPATCH® Cu GigaSPEED X10D® U/UTP Riser Preterminated Copper Cable, dual row OneLink 2x6 to unterminated, 12 links

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Copper trunk cable assembly   |
| <b>Product Brand</b>         | GigaSPEED X10D®   InstaPATCH® Cu                                    |

## General Specifications

|                                       |                    |
|---------------------------------------|--------------------|
| <b>ANSI/TIA Category</b>              | 6A                 |
| <b>Cable Type</b>                     | U/UTP (unshielded) |
| <b>Conductor Type</b>                 | Solid              |
| <b>Interface, Connector A</b>         | OneLink 2x6        |
| <b>Interface Feature, connector A</b> | Standard           |
| <b>Interface, Connector B</b>         | Unterminated       |
| <b>Link Count</b>                     | 12                 |
| <b>Wiring</b>                         | T568B              |

## Dimensions

|   |        |
|---|--------|
| <b>Cable Assembly Length Range (m)</b>  | 2 – 30 |
| <b>Cable Assembly Length Range (ft)</b> | 7 – 98 |

## Electrical Specifications

|                               |         |
|-------------------------------|---------|
| <b>dc Resistance, maximum</b> | 0.3 ohm |
| <b>Safety Voltage Rating</b>  | 300 V   |

## Ordering Tree

# CBSXD | IP6A-12RUTP-1LK12-BLUNT

|   |   |   |   |   |   |   |   |   |    |    |    |   |   |   |   |
|---|---|---|---|---|---|---|---|---|----|----|----|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |   |   |   |   |
| C | A | A | A | C | - | 1 | 1 | H | A  | B  | B  | F | 0 | 5 | 0 |

| Cable Type |                                     |
|------------|-------------------------------------|
| A          | Cat 6A X10D – U/UTP (Plenum)        |
| B          | Cat 6A X10D – U/UTP (Riser)         |
| C          | Cat 6A X10D – U/UTP (LSZH)          |
| D          | Cat 6A X10D – F/UTP (Plenum)        |
| E          | Cat 6A X10D – F/UTP (Riser)         |
| F          | Cat 6A X10D – F/UTP (LSZH)          |
| G          | Cat 6 XL – U/UTP (Plenum)           |
| H          | Cat 6 XL – U/UTP (Riser)            |
| J          | Cat 6 XL – U/UTP (LSZH)             |
| Q          | Cat 6A X10D – S/FTP (LSZH)          |
| R          | Cat 6 – U/UTP Class B Rated (LSZH)  |
| S          | Cat 6A – U/UTP Class B Rated (LSZH) |
| Y          | Cat 6A X10D SD – U/UTP (Riser)      |

| Connector B |  |
|-------------|--|
| A           | Outlet* – Single Row Standard Density    |
| B           | Outlet* – Dual Row Standard Density      |
| C           | Outlet* – Dual Row High Density          |
| G           | RJ45 Plug* – Single Row Standard Density |
| H           | RJ45 Plug* – Dual Row Standard Density   |
| J           | RJ45 Plug* – Dual Row High Density       |
| N           | 1100 Module                              |
| R           | 360 1100 Evolve Module                   |
| S           | OneLink 2x6                              |
| T           | OneLink 2x4                              |

| Orientation A |                       |
|---------------|-----------------------|
| 1             | Trident Series Flat   |
| 2             | Right Paired Flat     |
| 3             | Right Series Flat     |
| 4             | Left Paired Flat      |
| 5             | Left Series Flat      |
| 6             | Trident Paired Flat   |
| A             | Trident Series Angled |
| B             | Right Paired Angled   |
| C             | Right Series Angled   |
| D             | Left Paired Angled    |
| E             | Left Series Angled    |
| F             | Trident Paired Angled |

| Orientation B |                       |
|---------------|-----------------------|
| 1             | Trident Series Flat   |
| 2             | Right Paired Flat     |
| 3             | Right Series Flat     |
| 4             | Left Paired Flat      |
| 5             | Left Series Flat      |
| 6             | Trident Paired Flat   |
| A             | Trident Series Angled |
| B             | Right Paired Angled   |
| C             | Right Series Angled   |
| D             | Left Paired Angled    |
| E             | Left Series Angled    |
| F             | Trident Paired Angled |
| X             | Not Applicable        |

| Connector A |  |
|-------------|--|
| A           | Outlet* – Single Row Standard Density    |
| B           | Outlet* – Dual Row Standard Density      |
| C           | Outlet* – Dual Row High Density          |
| G           | RJ45 Plug* – Single Row Standard Density |
| H           | RJ45 Plug* – Dual Row Standard Density   |
| J           | RJ45 Plug* – Dual Row High Density       |
| N           | 1100 Module                              |
| R           | 360 1100 Evolve Module                   |
| S           | OneLink 2x6                              |
| T           | OneLink 2x4                              |
| X           | Unterminated                             |

| Link |    |
|------|----|
| B    | 6  |
| C    | 8  |
| D    | 12 |
| E    | 16 |
| F    | 18 |
| G    | 24 |

| Outlet Color |                |
|--------------|----------------|
| 0            | Not Applicable |
| 1            | Black (BK)     |
| 2            | Blue (BL)      |
| B            | White (WH)     |

| UOM |       |
|-----|-------|
| F   | Foot  |
| M   | Meter |

| Length |     |
|--------|-----|
| 12     | XXX |

| Bundling |             |
|----------|-------------|
| H        | Hook-n-loop |
| S        | Sleaving    |

| Jacket Color |            |
|--------------|------------|
| B            | White (WH) |
| C            | Slate (SL) |
| Z            | Blue (BL)  |

| Labeling |               |
|----------|---------------|
| A        | Generic Label |

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Environmental Space</b>   | Riser                                |
| <b>Flammability Rating</b>   | UL 94 V-0                            |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

|            |   |   |
|------------|---|---|
| 1095B-4/24 | – | GigaSPEED X10D® 1095B Category 6A U/UTP Cable, non-plenum, 4 pair count |
|------------|---|---|

# 1095B-4/24

---

GigaSPEED X10D® 1095B Category 6A U/UTP Cable, non-plenum, 4 pair count

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Product Type</b>          | Twisted pair cable  |
| <b>Product Brand</b>         | GigaSPEED X10D®   |


## General Specifications

|                                |                    |
|--------------------------------|--------------------|
| <b>Product Number</b>          | 1095B              |
| <b>ANSI/TIA Category</b>       | 6A                 |
| <b>Cable Component Type</b>    | Cordage            |
| <b>Cable Type</b>              | U/UTP (unshielded) |
| <b>Conductor Type, singles</b> | Solid              |
| <b>Conductors, quantity</b>    | 8                  |
| <b>Pairs, quantity</b>         | 4                  |
| <b>Separator Type</b>          | Isolator           |
| <b>Transmission Standards</b>  | ANSI/TIA-568.2-D   |

## Dimensions

|                                      |                     |
|--------------------------------------|---------------------|
| <b>Diameter Over Jacket, nominal</b> | 7.239 mm   0.285 in |
| <b>Jacket Thickness</b>              | 1.524 mm   0.06 in  |
| <b>Conductor Gauge, singles</b>      | 24 AWG              |

## Cross Section Drawing



## Electrical Specifications

|  |   |
|--|---|
| <b>Characteristic Impedance</b>              | 100 ohm   |
| <b>Characteristic Impedance Tolerance</b>    | ±15 ohm   |
| <b>dc Resistance Unbalance, maximum</b>      | 4 %   |
| <b>dc Resistance, maximum</b>                | 9.38 ohms/100 m   2.859 ohms/100 ft   |
| <b>Dielectric Strength, minimum</b>          | 1500 Vac   2500 Vdc   |
| <b>Mutual Capacitance at Frequency</b>       | 6.0 nF/100 m @ 1 kHz  |
| <b>Nominal Velocity of Propagation (NVP)</b> | 67 %  |
| <b>Operating Frequency, maximum</b>          | 550 MHz   |
| <b>Operating Voltage, maximum</b>            | 80 V  |
| <b>Remote Powering</b>                       | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |
| <b>Safety Voltage Rating</b>                 | 300 V   |

## Material Specifications

|                            |             |
|----------------------------|-------------|
| <b>Conductor Material</b>  | Bare copper |
| <b>Insulation Material</b> | Polyolefin  |

# 1095B-4/24

---

|                             |            |
|-----------------------------|------------|
| <b>Jacket Material</b>      | PVC        |
| <b>Separator Material</b>   | Polyolefin |
| <b>Separator 2 Material</b> | Polyolefin |

## Mechanical Specifications

|                                 |                  |
|---------------------------------|------------------|
| <b>Pulling Tension, maximum</b> | 11.34 kg   25 lb |
|---------------------------------|------------------|

## Environmental Specifications

|                                 |                                     |
|---------------------------------|-------------------------------------|
| <b>Installation temperature</b> | 0 °C to +60 °C (+32 °F to +140 °F)  |
| <b>Operating Temperature</b>    | -20 °C to +60 °C (-4 °F to +140 °F) |
| <b>Environmental Space</b>      | Non-plenum                          |
| <b>Flame Test Method</b>        | CM                                  |

## Packaging and Weights

|                     |                             |
|---------------------|-----------------------------|
| <b>Cable weight</b> | 55.047 kg/km   36.99 lb/kft |
|---------------------|-----------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |