

# 760082545 | RK4P45-29S



Equipment Rack, 4-Post, 29 in (737 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black

## OBSOLETE

### Replaced By:

760175703 RK-4PE-45-29S	Equipment Rack, 4-Post, 29 in (737 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black
760175729 RK-4PE-45-36S	Equipment Rack, 4-Post, 36 in (914 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	4 post rack

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	45
<b>Rail Mounting Hole</b>	3/8 in

## Dimensions

<b>Height</b>	2,133.6 mm   84 in
<b>Channel Width</b>	76.2 mm   3 in
<b>Width</b>	518.16 mm   20.4 in
<b>Depth</b>	1,041.4 mm   41 in
<b>Dimensional Standards</b>	EIA-310-E

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Steel

# 760082545 | RK4P45-29S

---

## Mechanical Specifications

**Load Rating** 907.185 kg | 2000 lb

## Environmental Specifications

**Safety Standard** UL | cUL

## Packaging and Weights

**Included** Base pan | Forty #12-24 x 1/2 in mounting screws | Forty M6 cage nuts | Four vertical rack rails | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

**Packaging quantity** 1

**Packaging Type** Flat packed

**Weight, net** 47.63 kg | 105.006 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system