



Rack, 2-Post, (58U), 3 in (76 mm) Channel x 9 ft (2743 mm) H x 23 in (584 mm) W, alum, 12-24 tapped rails, black

## OBSOLETE

This product was discontinued on: November 30, 2018

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	2 post rack

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 23 in
<b>Rack Units</b>	58
<b>Rail Mounting Hole</b>	#12-24

## Dimensions

<b>Height</b>	2,743.2 mm   108 in
<b>Channel Width</b>	76.2 mm   3 in
<b>Width</b>	515.62 mm   20.3 in
<b>Depth</b>	381 mm   15 in
<b>Dimensional Standards</b>	EIA-310-D

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Aluminum

## Mechanical Specifications

<b>Load Rating</b>	453.592 kg   1000 lb
--------------------	----------------------

## Packaging and Weights

**Included** Forty #12-24 x 1/2 in mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

**Packaging quantity** 1

**Packaging Type** Flat packed

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system