

FL2-96SPNL2

FL2000 Fiber Splice Panel, unloaded, for 96 splices, 19 in, 4RU, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Series	FL2000

General Specifications

Functionality	Splicing
Cable Exit Location	Rear, left side Rear, right side
Color	Putty white
Color, front	Putty white
Growth Configuration	Unloaded
Interface, front	Unloaded
Patching Capacity, maximum	0
Rack Type	EIA 19 in
Rack Units	4
Shelf Movement	Hinged
Splicing Capacity, maximum	96

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	256.54 mm 10.1 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

FL2-96SPNL2

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

