

FL2-R770072A0-0A00

FL2000 Fiber Termination Panel, 72 SC/UPC, singlemode, 5RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FL2000

General Specifications


Functionality	Patching
Adapter Packs Included, quantity	12
Color	Putty white
Color, front	Putty white
Growth Configuration	Fully loaded
Interface, front	SC
Interface Feature, front	Standard
Patching Capacity, maximum	72
Rack Type	EIA 19 in
Rack Units	5
Shelf Movement	Hinged
Splicing Capacity, maximum	0
Total Ports, quantity	72

Dimensions

Height	222.25 mm 8.75 in
Width	482.6 mm 19 in
Depth	257 mm 10.118 in

Ordering Tree

FL2-R770072A0-0A00



Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

Regulatory Compliance/Certifications

FL2-R770072A0-0A00

Agency

CHINA-ROHS
REACH-SVHC
ROHS

Classification

Above maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant/Exempted

