UFVLCUC42

Base Product



Ultra Low Loss (ULL) LazrSPEED® 550 WideBand OM5 LC/UPC to Unconnectorized, Fiber Pigtail, 1.6 mm Duplex, LSZH

Product Classification

Regional Availability	Asia Australia/New Zealand Europe Latin America Middle East /Africa North America	
Portfolio	CommScope®	
Product Type	Fiber pigtail, jacketed	
Product Brand	SYSTIMAX ULL	
Product Series	UFV	
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration	
General Specifications		

י שאברוונסנוט

Color, connector A	Beige
Interface, Connector A	LC/UPC
Jacket Color	Lime green
Total Fibers, quantity	2

Dimensions

Cable Assembly Length Range (m)	1 – 61
Cable Assembly Length Range (ft)	2 - 200
Diameter Over Jacket	1.6 mm 0.063 in

Ordering Tree

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024



UFVLCUC42

	BASE	CODE	-	N X			
	acket Color	Bra	akout Length / Opti	on	I	JOM	Length
J	acket Color	Die	akout Length / Opti	on			
ر ۱	Lime green	X	No breakout	on	F	Feet	8

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
Optical Specifications	
Fiber Mode	Multimode

Fiber Type	OM5, LazrSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Dual Rated LSZH/Riser

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

760233361 P-002-ZC-5G-F16LM	
860637378	

- Fiber indoor cable, LazrSPEED® 1.6 mm Plenum Zipcord, Multimode OM5, Feet jacket marking, Lime green jacket color
- LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024

