
FNWSCSCAH

Base Product



SingleMode SC/UPC to SC/UPC, InstaPATCH® 360 Ruggedized Fiber Fanout Cable Assembly, 48-Fiber, Low Smoke Zero Halogen (LSZH)

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX InstaPATCH® 360

Ordering NoteFor lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration | Not available in the United States or Canada

General Specifications

Color, boot A Blue

Color, connector A Blue

Color, boot B Blue

Color, connector B Blue

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A SC/UPC

Interface, Connector B SC/UPC

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 48

Dimensions

Cable Assembly Length Range (m) 3 - 305


Cable Assembly Length Range (ft) 8 - 999

Page 1 of 8



FNWSCSCAH

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 2 of 8



FNWSCSCAH

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant



N-048-MP-8W-F12

Included Products

460125768 – TeraSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Duplex, Singlemode

 Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.652.D and G.657.A1, Feet jacket marking, Dca flame rating



460125768

TeraSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Duplex, Singlemode

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandTeraSPEED®

General Specifications

Body StyleDuplexColorBlue

Ferrule Geometry Pre-radiused

Interface SC/UPC

Dimensions

 Length
 56 mm | 2.205 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, typical0.3 dBReturn Loss, minimum55 dB

Packaging and Weights



460125768

Packaging quantity

2

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)



N-048-MP-8W-F12

Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.652.D and G.657.A1, Feet jacket marking, Dca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-freeJacket MarkingFeet

Subunit, quantity 4

Fibers per Subunit, quantity 12


Total Fiber Count 48

Dimensions

Buffer Tube/Subunit Diameter 3 mm | 0.118 in

Diameter Over Jacket 9.2 mm | 0.362 in

Representative Image



Page 6 of 8

N-048-MP-8W-F12

Mechanical Specifications

Minimum Bend Radius, loaded138 mm | 5.433 inMinimum Bend Radius, unloaded92 mm | 3.622 inTensile Load, long term, maximum400 N | 89.924 lbfTensile Load, short term, maximum1335 N | 300.12 lbfCompression10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

 Flex Test Method
 FOTP-104 | IEC 60794-1 E6

 Impact
 5.88 N-m | 52.042 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2 | OS2

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 °F to +140 °F)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga2

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

COMMSCOPE®

N-048-MP-8W-F12

Environmental Test Specifications

Heat Age $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-4 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Heat Age Test Method IEC 60794-1 F9

Low High Bend -20 °C to +70 °C (-4 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 72 kg/km | 48.382 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

CENELEC

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

