

HLT4-PNMNR-3-AR1



HLT4-50T Jumper with interface types 7-16 DIN Male and N Male Right Angle, 1.01 m

OBSOLETE

This product was discontinued on: November 15, 2007

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX®
Product Series	HLT4-50T

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	7-16 DIN Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	1.01 m 3.314 ft
Nominal Size	1/2 in

Electrical Specifications

DTF, Connector A	-32 dB
DTF, Connector B	-32 dB

Jumper Assembly Sample Label

HLT4-PNMNR-3-AR1



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

- | | | |
|-----------|---|--|
| HLT4-50T | - | HLT4-50T, HELIAX® High Power, High Temperature Air Dielectric Coaxial Cable, corrugated copper, 1/2 in, blue PVDF jacket |
| L4TDM-PS | - | 7-16 DIN Male Positive Stop™ for 1/2 in LDF4-50A cable |
| L4TDM-PSA | - | 7-16 DIN Male Positive Stop™ for 1/2 in AL4RPV-50, LDF4-50A, HL4RPV-50 cable |
| L4TNR-HC | - | Type N Male Right Angle for 1/2 in LDF4-50A cable |