APT-BDFDF-DB



Arrestor Plus® Dual Band Quarterwave Surge Arrestor (T-shaped), 806– 960 MHz and 1700–2170 MHz, with interface types DIN Female Bulkhead and DIN Female

Product Classification

Product Type	Quarter wave shorting stub
Product Brand	Arrestor Plus®
Ordering Note	ANDREW® non-standard product
General Specifications	
Device Type	dc Block
Body Style	Bulkhead
Inner Contact Plating	Silver
Interface	7-16 DIN Female Bulkhead
Interface 2	7-16 DIN Female
Outer Contact Plating	Trimetal
Pressurizable	No
Dimensions	
Height	75 mm 2.953 in
Width	42 mm 1.654 in
Length	80 mm 3.15 in
Electrical Specifications	
3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss, typical	0.07 dB
Average Power at Frequency	3,000.0 W @ 900 MHz
Connector Impedance	50 ohm
Lightning Surge Capability	100 times @ 20 kA
Lightning Surge Capability Test Method	IEEE C62.42-1991
Lightning Surge Capability Waveform	8/20 waveform

Page 1 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

APT-BDFDF-DB

Lightning Surge Current	30 kA
Lightning Surge Current Waveform	8/20 waveform
Operating Frequency Band	1710 – 2000 MHz 2000 – 2170 MHz 806 – 960 MHz
Peak Power, maximum	40 kW
Throughput Energy at Current	2.0 mJ @ 30 kA 25.0 µJ @ 2 kA
Throughput Energy Waveform	8/20 waveform

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
806–960 MHz	1.106	25.96
1710–2000 MHz	1.119	25.01
2000–2170 MHz	1.106	25.96

Mechanical Specifications

Attachment Durability	25 cycles
Interface Durability	500 cycles
Interface Durability Method	IEC 61169-16:9.5
Mechanical Shock Test Method	MIL-STD-202F, Method 213B, Test Condition C

Environmental Specifications

Operating Temperature	-40 °C to +150 °C (-40 °F to +302 °F)
Storage Temperature	-40 °C to +100 °C (-40 °F to +212 °F)
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Corrosion Test Method	MIL-STD-202, Method 101, Test Condition B
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Moisture Resistance Test Method	MIL-STD-202, Method 106
Thermal Shock Test Method	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 $^\circ\mathrm{C}$
Vibration Test Method	GR 2846-CORE
Water Jetting Test Mating	Mated



Page 2 of 3

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

APT-BDFDF-DB

Packaging and Weights

Weight, net

0.63 kg | 1.39 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 3 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025