

HBXX-9014DS-VTM | HBXX-9014DS-A2M



4-port sector antenna, 4x 1710–2180 MHz, 90° HPBW, RET compatible

- Enhanced control of out-of-sector power improves co-channel interference, reduces softer hand-offs, improves capacity

This product will be discontinued on: December 31, 2025

General Specifications

Antenna Type	Sector
Band	Single band
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	PVC, UV resistant
Radiator Material	Low loss circuit board
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, high band	4
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	0
RF Connector Quantity, total	4

Remote Electrical Tilt (RET) Information

Model with Factory Installed AISG 2.0 Actuator	HBXX-9014DS-A2M
---	-----------------

Dimensions

Width	305 mm 12.008 in
Depth	166 mm 6.535 in
Length	1297 mm 51.063 in
Net Weight, without mounting kit	13.5 kg 29.762 lb

HBXX-9014DS-VTM | HBXX-9014DS-A2M

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1710 – 2180 MHz
Polarization	±45°

Electrical Specifications

Frequency Band, MHz	1710–1880	1850–1990	1920–2180
Gain, dBi	16	16	16.2
Beamwidth, Horizontal, degrees	88	88	88
Beamwidth, Vertical, degrees	7.5	7.1	6.7
Beam Tilt, degrees	0–10	0–10	0–10
USLS (First Lobe), dB	17	17	18
Front-to-Back Ratio at 180°, dB	30	30	30
Isolation, Cross Polarization, dB	30	30	30
VSWR Return loss, dB	1.4 15.6	1.4 15.6	1.4 15.6
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150
Input Power per Port, maximum, watts	350	350	350

Mechanical Specifications

Wind Loading @ Velocity, frontal	420.0 N @ 150 km/h (94.4 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	113.0 N @ 150 km/h (25.4 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	488.0 N @ 150 km/h (109.7 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	409 mm 16.102 in
Depth, packed	292 mm 11.496 in
Length, packed	1609 mm 63.346 in
Weight, gross	22.1 kg 48.722 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value

HBXX-9014DS-VTM | HBXX-9014DS-A2M

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 600899A-2 – Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance