

RFFT-6SM-002-10M

HELIAX® Discrete, Bend Insensitive Singlemode Fiber DLC to DLC 6-Fiber Cable Assembly, 10 m



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	RFFT
Ordering Note	CommScope® non-standard product

General Specifications

Construction Type	Discrete fiber trunk
Interface, Connector A	LC/UPC
Interface Feature, connector A	Uniboot
Interface Body Style, connector A	Straight
Interface, Connector B	LC/UPC
Interface Feature, connector B	Uniboot
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	6

Dimensions

Cord Length	10 m 32.808 ft
Diameter Over Jacket	10.3 mm 0.406 in

Mechanical Specifications

Minimum Bend Radius	103 mm 4.055 in
----------------------------	-------------------

RFFT-6SM-002-10M

Minimum Bend Radius, furcation 30 mm | 1.181 in

Optical Specifications

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Indoor

Packaging and Weights

Cable weight 136 kg/km | 91.388 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)