

IMDLOAD-110M



Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	PTS1-50-HRL

General Specifications

Body Style, Connector A	Panel mount
Interface, Connector A	7-16 DIN Female
Interface, Connector B	Sold separately
Specification Sheet Revision Level	A

Dimensions

Length	110 m 360.892 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD	-125 dBm
----------------------	----------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.05

Jumper Assembly Sample Label

IMDLOAD-110M



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition