

DB224-C



1-port omni exposed dipole antenna, 164–174 MHz, 360° HPBW, fixed electrical tilt

- Broad response
- Two-piece mast for ease of shipping

General Specifications

Antenna Type	Omni
Band	Single band
Color	Silver
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radiator Material	Aluminum
RF Connector Interface	N Male
RF Connector Location	Bottom
RF Connector Quantity, high band	0
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

Dimensions

Length	6477 mm 255 in
Net Weight, without mounting kit	15.9 kg 35.053 lb

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	164 – 174 MHz
Polarization	Vertical

Electrical Specifications

Frequency Band, MHz	164–174
Gain, dBi	8.1
Beamwidth, Horizontal,	360

DB224-C

degrees

Beamwidth, Vertical, degrees	16
Beam Tilt, degrees	0
VSWR Return loss, dB	1.5 14.0
Input Power per Port, maximum, watts	500

Mechanical Specifications

Wind Loading @ Velocity, maximum	560.5 N @ 100 mph (126.0 lbf @ 100 mph)
Wind Speed, maximum	130 km/h (81 mph)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

DB365-OS	-	Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.
----------	---	---

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---