


RV65A-2X2



4-port sector antenna, 2x 694–960 and 2x 1695–2690 MHz, 65° HPBW, RET compatible

- Utilizes AccuRET® actuator(s) on the back of the antenna

OBSOLETE

This product was discontinued on: **March 31, 2023**

Replaced By:

RV-65A-R2

4-port sector antenna, 2x 694–960 and 2x 1695–2690 MHz, 65° HPBW, 2x RET

General Specifications


Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-EN
Radome Material	Fiberglass, UV resistant
Radiator Material	Aluminum Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, high band	2
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	2
RF Connector Quantity, total	4

Dimensions

Width	301 mm 11.85 in
Depth	181 mm 7.126 in
Length	1412 mm 55.591 in
Net Weight, without mounting kit	17.1 kg 37.699 lb

RV65A-2X2

Array Layout



Array	Freq (MHz)	Conns
R1	694-960	1-2
Y1	1695-2690	3-4

Bottom

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration

RV65A-2X2



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	800 W @ 50 °C

Electrical Specifications

Frequency Band, MHz	694–703	703–790	790–890	890–960	1695–1920	1920–2180	2300–2690
Gain, dBi	13.6	13.7	14	14.3	17.1	17.5	18.1
Beamwidth, Horizontal, degrees	72	73	71	69	64	65	60
Beamwidth, Vertical, degrees	17.3	16.6	15.3	14	7.2	6.4	5.3
Beam Tilt, degrees	2–15	2–15	2–15	2–15	2–12	2–12	2–12
USLS (First Lobe), dB	20	20	19	17	16	14	14
Front-to-Back Ratio at 180°,	27	29	33	31	28	30	31

RV65A-2X2

dB

Isolation, Cross Polarization, dB	25	28	28	28	28	28	28
Isolation, Inter-band, dB	30	30	30	30	30	30	30
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	300	300	300	300	250	250	250

Mechanical Specifications

Wind Loading @ Velocity, frontal	205.0 N @ 150 km/h (46.1 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	169.0 N @ 150 km/h (38.0 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	396.0 N @ 150 km/h (89.0 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	208.0 N @ 150 km/h (46.8 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	429 mm 16.89 in
Depth, packed	329 mm 12.953 in
Length, packed	1672 mm 65.827 in
Weight, gross	30.5 kg 67.241 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

BSAMNT-OFFSET	–	Forward Offset Pipe Mounting Kit for 4.5 in (114.3 mm) OD round members
---------------	---	---

RV65A-2X2

* Footnotes

Performance Note

Severe environmental conditions may degrade optimum performance



BSAMNT-OFFSET



Forward Offset Pipe Mounting Kit for 4.5 in (114.3 mm) OD round members

Product Classification

Product Type Pipe mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 114.3 mm | 4.5 in

Compatible Diameter, minimum 61 mm | 2.402 in

Weight, net 3.5 kg | 7.716 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



BSAMNT-OFFSET

