

760187989



RBA84-36 GE 8RU 48/24V, HEX / Saft-DAC, Power & Battery Cabinet

- Sealed to outside environment
- Double wall construction

OBSOLETE

Product Classification

Product Type Power supply enclosure

General Specifications

Access Front door | Rear door

Batteries Not included

Batteries Supported 180 A-h batteries

Cabinet Type Battery back-up cabinet

Color Beige

Cooling Heat exchange

Dimensions

Height 2,133.6 mm | 84 in

Width 914.4 mm | 36 in

Depth 990.6 mm | 39 in

Electrical Specifications

Battery String Current, maximum 1260 A-h @ 48 Vdc

Battery Strings, quantity 6 @ -48 Vdc

Voltage 24 Vdc | 48 Vdc

Material Specifications

Finish Powder coated

Environmental Specifications

760187989

Qualification Standards OSHA | Telcordia GR-487

Packaging and Weights

Weight, net 362.874 kg | 800 lb

Weight, with batteries, typical 1,451.496 kg | 3200 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system