

## XAGA® 1000

### Pressurized heat-shrinkable copper splice closure

The XAGA® 1000 pressurized splice closure system provides a fast, simple way to seal telephone cable splices in pressurized telephone cable. The XAGA® 1000 splice closure is used for aerial, buried, and underground applications on polyethylene or lead sheathed cable in sizes up to 3600 pairs. XAGA® 1000 closure kits are simple and easy to install. The wraparound sleeve design accommodates most cable sizes with just a few kit sizes, reducing inventories.




### Features and benefits

- Composite material provides high mechanical strength
- Range of closures to suit all cable sizes
- Applicable for polyethylene and metal jacketed cables
- Pre-installed valve for pressure access and measuring
- Suitable for use with all standard connector systems
- Up to 4 cables out at each end
- Wraparound closure suitable for both maintenance and new construction
- Interchangeable air valve/connector
- Hotmelt adhesive designed specifically for pressurized closure applications

### Specifications

#### General attributes & mechanical characteristics

#### XAGA® 1000 – International valve



Product description	Splice bundle dia. max. (A) (mm)	Single cable dia. min. (B) (mm)	Sheath opening nom. (L) (mm)
XAGA-1000C-45/8-350A340	45	8	350
XAGA-1000C-62/15-250A340	62	15	250
XAGA-1000C-62/15-350A340	62	15	350
XAGA-1000C-62/15-500A340	62	15	500
XAGA-1000C-62/15-650A340	62	15	650
XAGA-1000C-92/30-350A340	92	30	350
XAGA-1000C-92/30-500A340	92	30	500
XAGA-1000C-92/30-650A340	92	30	650
XAGA-1000-160/55-720A340	160	55	720
XAGA-1000-160/55-900A340	160	55	900
XAGA-1000-200/65-500A340	200	65	500
XAGA-1000-200/65-720A340	200	65	720

XAGA-1000-200/65-900A340	200	65	900
--------------------------	-----	----	-----

## XAGA® 1000 – US valve

Product description	Splice bundle dia. max. (A) (mm)	Single cable dia. min. (B) (mm)	Sheath opening nom. (L) (mm)
XAGA-1000-62/15-350A341	62	15	350
XAGA-1000-92/30-650A341	92	30	650
XAGA-1000-122/38-500A341	122	38	500
XAGA-1000-122/38-650A341	122	38	650
XAGA-1000-160/55-500A341	160	55	500
XAGA-1000-160/55-720A341	160	55	720
XAGA-1000-160/55-900A341	160	55	900
XAGA-1000-200/65-500A341	200	65	500
XAGA-1000-200/65-720A341	200	65	720
XAGA-1000-200/65-900A341	200	65	900

## XAGA® 1000 kit content

- Abrasive strip
- Aluminum closing strip
- Aluminum tape
- Cleaning tissue
- Flexible stainless-steel channels
- Heat-shrinkable sleeve
- Installation instruction
- Metal canister (2 half shells)
- Shield continuity wire
- Underclips
- Valve nut + 1 valve plug + 1 valve insert



## **Accessories**

Description	To be used in
BOKT-1000-05	XAGA-1000C-45/8-350
BOKT-1000-6	XAGA-1000C-62/15-xxx and XAGA-1000C-92/30-xxx and XAGA-1000-122/38-xxx
BOKT-1000-7	XAGA-1000-160/55-xxx and XAGA-1000-200/65-xxx

## BOKT kit content

- Abrasive strip
- Aluminium tape
- Branch-off clip
- Cleaning tissue
- Shield continuity wire + connector
- Tie wrap



commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2018 CommScope, Inc. All rights reserved.

Unless otherwise noted, all trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability with a number of CommScope's facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001.

Further information regarding CommScope's commitment can be found at [www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability](http://www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability).

Document number PA-113043-EN