760249703 | 0-024-CA-8Z-M24BK/28G/093



Fiber OSP cable, PE, Gel-filled Central Tube, CST, 24 fiber, Singlemode G. 652.D and G.657.A1, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series O-CA

General Specifications

Cable Type Central loose tube

Construction Type Armored
Subunit Type Gel-filled
Jacket Color Black
Jacket Marking Feet
Fibers per Subunit, quantity 24
Total Fiber Count 24

Dimensions

Buffer Tube/Subunit Diameter 2.8 mm | 0.11 in

Diameter Over Jacket 9.1 mm | 0.358 in

Mechanical Specifications

Minimum Bend Radius, loaded182 mm | 7.165 inMinimum Bend Radius, unloaded91 mm | 3.583 inTensile Load, long term, maximum890 N | 200.08 lbfTensile Load, short term, maximum2700 N | 606.984 lbfCompression20 N/mm | 114.203 lb/in

Compression Test Method IEC 60794-1-2 E3

COMMSCOPE®

760249703 | 0-024-CA-8Z-M24BK/28G/093

Flex 25 cycles

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-2-E1

Optical Specifications

Fiber Type G.652.D and G.657.A1 | OS2

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.22 dB/km @ 1,550 nm | 0.38 dB/km @ 1,310 nm

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Buried | Ducted | Outdoor

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5B

Environmental Test Specifications

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 92 kg/km | 61.821 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products



760249703 | 0-024-CA-8Z-M24BK/28G/093

CS-8Z-LT

 Low Water Peak, Dispersion-Unshifted Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable