

Fiber OSP cable, PE, Stranded Loose Tube Gel-filled CST, 48 fiber, Multimode OM4, Meters jacket marking, Black jacket color

Product Classification

Regional Availability	Asia Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LA


General Specifications

Cable Type	Stranded loose tube
Construction Type	Armored
Fiber Type, quantity	48
Fibers per Subunit, quantity	12
Jacket Color	Black
Jacket Marking	Meters
Subunit Type	Gel-filled
Total Fiber Count	48

Dimensions

Buffer Tube/Subunit Diameter	2.2 mm 0.087 in
Diameter Over Jacket	12.2 mm 0.48 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	240 mm 9.449 in
Minimum Bend Radius, unloaded	120 mm 4.724 in
Tensile Load, short term, maximum	2700 N 606.984 lbf
Compression	22 N/mm 125.623 lb/in
Compression Test Method	IEC 60794-1-2 E3
Flex	25 cycles
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1

Optical Specifications

Fiber Type	OM4
-------------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	1.00 dB/km @ 1,300 nm 3.00 dB/km @ 850 nm
-----------------------------	---

Environmental Specifications

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Buried Ducted Outdoor
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5B

Environmental Test Specifications

Temperature Cycle -30 °C to +70 °C (-22 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 140 kg/km | 94.076 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable