

CPC2282



GigaSPEED XL® MGS400 to MGS400 on 1071 Solid Cable Pre-terminated Cord

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Twisted pair patch cord |
| Product Brand | GigaSPEED XL® |
| Product Series | CPC |
| Ordering Note | Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices |

General Specifications

| | |
|---------------------------------------|--|
| ANSI/TIA Category | 6 |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Solid |
| Information Outlet Color | Black Blue Gray Green Ivory Orange Red White Yellow |
| Interface, Connector A | Information outlet |
| Interface Feature, connector A | Standard |
| Interface, Connector B | Information outlet |
| Interface Feature, connector B | Standard |
| Jacket Color | Black Blue Dark gray Light blue Lilac Orange Red Slate Spring green White Yellow |
| Pairs, quantity | 4 |
| Transmission Standards | IEEE 802.3bt Type 4 |
| Wiring | T568B |

CPC2282

Dimensions

| | |
|--|--------------------|
| Cable Assembly Length Range (m) | 1 – 100 |
| Cable Assembly Length Range (ft) | 1 – 328 |
| Diameter Over Jacket | 5.89 mm 0.232 in |
| Compatible Conductor Gauge, solid | 23 AWG |

Wiring Diagram

| | Connector A | Connector B |
|------------|--------------|--------------|
| Position 1 | White/Orange | White/Orange |
| Position 2 | Orange | Orange |
| Position 3 | Lt. Green | Lt. Green |
| Position 4 | Blue | Blue |
| Position 5 | Lt. Blue | Lt. Blue |
| Position 6 | Green | Green |
| Position 7 | Lt. Brown | Lt. Brown |
| Position 8 | Brown | Brown |

Electrical Specifications

| | |
|-------------------------------|---------|
| dc Resistance, maximum | 0.3 ohm |
| Safety Voltage Rating | 300 V |

Ordering Tree

CPC2282

CPC - ⁹ ¹⁰ ¹¹ ¹²

Outlet Color

| | | |
|---|---|----------------|
| 9 | 0 | Not applicable |
| | 1 | Black |
| | 2 | Blue |
| | 3 | Gray |
| | 4 | Green |
| | 5 | Ivory |
| | 6 | Orange |
| | 7 | Red |
| | 8 | White |
| | 9 | Yellow |
| | B | Lilac |

Jacket Color

| | | |
|----|---|--------------|
| 10 | 1 | Black |
| | 2 | Light blue |
| | 3 | Dark gray |
| | 4 | Spring green |
| | 5 | Ivory |
| | 6 | Orange |
| | 7 | Red |
| | 8 | White |
| | 9 | Yellow |
| | B | Lilac |
| | C | Gray |
| | K | Pink |
| | L | Violet |
| | M | Green |
| | Z | Blue |

UOM

| | | |
|----|---|------------|
| 11 | F | Foot |
| | M | Meter |
| | N | Inch |
| | C | Centimeter |

Length

12

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

| | |
|---------------------------------|------------------------------|
| Contact Plating Material | Precious metals |
| Material Type | Copper alloy Polycarbonate |

Mechanical Specifications

| | |
|--------------------------------------|------------------|
| Plug Insertion Life, minimum | 750 times |
| Plug Retention Force, minimum | 133 N 29.9 lbf |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Environmental Space | Non-plenum |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | ETL cETL |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| | |
|---------------|--|
| Agency | Classification |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

