


760249994 | C-096-LA-5K-M12BK/25G/GY/FS



Fiber indoor/outdoor cable, LazrSPEED®, Single Jacket/Single Armor, 120 min Fire Survival, LSZH, 96 fiber, Gel-Filled, Stranded Loose Tube, Multimode OM4, Meters jacket marking, Black jacket color. Provides Rodent Resistance

- Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-LA


General Specifications

Armor Type	Corrugated steel
Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB F.O. CABLE 760249994 INT/EXT FIRE SURVIVAL 96 X 50 /125 OM4 (Serial NUMBER) (METRE MARK)
Subunit, quantity	8
Fibers per Subunit, quantity	12
Total Fiber Count	96

Dimensions

Buffer Tube/Subunit Diameter	2.5 mm 0.098 in
Diameter Over Jacket	16 mm 0.63 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	330 mm 12.992 in
Minimum Bend Radius, unloaded	200 mm 7.874 in
Tensile Load, long term, maximum	2000 N 449.618 lbf
Tensile Load, short term, maximum	4000 N 899.236 lbf
Compression	20 N/mm 114.203 lb/in
Compression Test Method	IEC 60794-1 E3
Impact	5 N-m 44.254 in lb
Impact Test Method	IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1 E1
Twist	5 cycles
Twist Test Method	IEC 60794-1 E7

Optical Specifications

Fiber Type	OM4 OM4, LazrSPEED®
-------------------	-----------------------

Environmental Specifications

Operating Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	EN 187105 IEC 60794-1-2

760249994 | C-096-LA-5K-M12BK/25G/GY/FS

Environmental Space	Aerial, lashed Buried Low Smoke Zero Halogen (LSZH)
Flame Test Method	IEC 60331-25 (120) Fire resistance: 120 minutes at 750 °C (no fiber break) IEC 60332-1 IEC 60754-1 IEC 60754-2 IEC 61034-2 NES 713 (<=5 - jacket material only)
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5

Environmental Test Specifications

Low High Bend Test Method	IEC 60794-1 E11
Temperature Cycle	-30 °C to +70 °C (-22 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1 F1

Packaging and Weights

Cable weight	304 kg/km 204.279 lb/kft
---------------------	----------------------------

Included Products

- CS-5K-LT - LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable