

Base Product



NOVUX™ SEC Splice/Patch Closure

The NOVUX SEC closure design is optimized for building façade applications. The SEC closure connects as many as eight customers and is agnostic to connectivity technologies (splice, connector, field-installable connector) for agility and flexibility. The innovative removable hinge design allows cover to open from the left, right, or top. Optional hinge locking mechanism is available for extra security. Identification plate for either QR code or customer logo are available.

The SEC closure is offered in two types:

SEC3:

Color is black (RAL 9005)

SEC4:

Color is gray (RAL 7035)

Key features of the NOVUX closures:

- NOVUX is the industry's most flexible FTTX platform. It takes modularity to new levels with technologies that span the end-to-fiber network from the trunk to the drop. That makes it the go-to FTTX platform for virtually every application today and in the future.
- NOVUX was designed from the ground up to help service providers gain access to the supplies they need –when and where they need them. And with the power of CommScope's global supply chain, service providers can trust that they'll be able to tackle even the largest FTTX deployments.
- With NOVUX, ordering, configuration, and training are all easier on the service provider's staff. With common components and installation procedures, it helps overcome craft labor shortages and reduce field errors, too.

Product Classification

Regional Availability	EMEA
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	In-line, rectangular fiber closure
Product Brand	NOVUX™
Product Series	SEC

General Specifications

Cable Capacity, Branch	2 Round 8.0–12.0 mm (0.31–0.47 in)
Cable Capacity, Drop	6 Round 3.0–6.0 mm (0.12–0.23 in) for pre-connectorized cables 6 Round 3.0–7.0 mm (0.12–0.27 in)


SEC

Cable Capacity, Feeder	2 Round 8.0–12.0 mm (0.31–0.47 in)
Cable Ports Quantity, total	10 round ports
Cable Sealing Type	Gasket/grommet configuration
Closure Sealing Type	Hinged with lock
Closure Style	In-line
Color	Black Gray
Mounting	Facade Wall
Network Area Type	Drop
Splicing Type, Supported	Single fusion

Dimensions

Height	130 mm 5.118 in
Width	216 mm 8.504 in
Depth	87 mm 3.425 in

Dimension Drawing



Port Configuration


SEC



Specifications	
Orientation	In-line
Connectivity technology	Splice only
Splice capacity (SMOUV 45 type)	12 splices
Adapters	(N/A)
Splitter quantity	As many as 1 per tray
Feeder cable type	Retractable cable
Feeder port size	9-12 mm (rubber), 0.35 inch – 0.47 inch
Feeder port quantity	2
Branch port size	1.8-7 mm (rubber), 0.07 inch – 0.27 inch
Branch port quantity	2
Drop port size, Single	1.8-7 mm (rubber), 0.07 inch – 0.27 inch
Drop port quantity, Single	6
Dimensions	210(W) x 117(D) x 50(H) mm 8.27(W) x 4.6(D) x 1.97(H) inches
Sealing level	IP 55
Color	Black RAL9005 or gray RAL7035

(*Upgrade kit includes one cover and two additional trays, and increases splice capacity from 12 to 36 splices.)

Ordering Tree



Optical Specifications

Fiber Type

G.657.A1 | G.657.A2 | G.657.B3

Environmental Specifications

SEC

Environmental Space Facade | Outdoor

Qualification Standards IP55

UV Resistance UV stabilized

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system